





No.	Order-No.	Designation	Material	H	a	O-Rings
Housings						
52 400 148		InClean776/200 DN25	1.4435	200	450	Viton
52 400 152		InClean776/200 DN25 Opt.298	1.4435	200	450	Viton
52 400 154		InClean776/200 DN25 Opt.363	1.4435	200	450	Viton
52 400 418		InClean776 DN25 363/437	1.4435	200	450	Viton
52 400 367		InClean776/200 DN25 Opt.437	1.4435	200	450	Viton
52 400 156		InClean776/200 D16-50	1.4435	200	450	Viton
52 400 361		Inclean776/200 D16-50 opt.437	1.4435	200	450	Viton
52 400 150		InClean776/200 DN25 C22/Ka	HA-C22	200	450	Kalrez
52 400 158		InClean776 D16-50 C22/Ka	HA-C22	200	450	Kalrez
52 400 556		InClean776 D16-50 Ti/Ka/437	Titanium	200	450	Kalrez
52 400 444		InClean777/200 A 150-2*	1.4435	200	425	Viton
52 400 183		InClean777 A 150-2 298/437	1.4435	200	425	Viton
52 401 033		InClean777/200 A 150-2* Opt.363	1.4435	200	425	Viton
52 400 147		InClean777/200 DN25	1.4435	200	425	Viton
52 400 151		InClean777/200 DN25 Opt.298	1.4435	200	425	Viton
52 400 153		InClean777/200 DN25 Opt.363	1.4435	200	425	Viton
52 400 182		InClean DN25 363/437	1.4435	200	425	Viton
52 400 192		InClean777/200 DN25 Opt.437	1.4435	200	425	Viton
52 400 155		InClean777/200 D16-50	1.4435	200	425	Viton
52 401 449		InClean777/200 DN25/Ka Opt.363	1.4435	200	425	Kalrez
52 400 171		InClean777/200 D16-50 Opt.437	1.4435	200	425	Viton
52 400 157		InClean777 D16-50 C22/Ka	HA-C22	200	425	Kalrez
52 400 478		InClean777 DN25 C22/Ka 437	HA-C22	200	425	Kalrez

Options:

No designation: 230V AC 48..62 Hz
 363: 115V AC 48..62 Hz
 298: 24V AC/DC 48..500Hz
 437: *T* and check valve for chemical cleaning

Pos.	Order-No.	Designation	Material
InClean776			
1a	00 764 1236	Cable grommet d=5 mm	Neoprene
1b	00 764 1237	Cable grommet d=7 mm	Neoprene
2	00 764 1283	Protective sleeve	Polypropylene
3a	00 764 2073	Ring nut compl.	Teflon
3b	00 764 1140	Top piece	Polypropylene
4	00 764 1060	Nut	Nickel-plated brass
5a	00 764 1058	Ring nut M60	Nickel-plated brass
5b	00 764 1059	Ring nut M60	1.4435

Mettler-Toledo GmbH, Process Analytics

Industrie Nord
 CH-8902 Urdorf
 Subject to technical changes. Mettler-Toledo GmbH

52900026 A/27 B

Pos.	Order-No.	Designation	Material
6	00 764 1065	Gasket 764-32.2	Neoprene
7	00 764 1064	Glass cylinder	Glass
8a	00 764 1054	Metal cylinder	Nickel-plated brass
8b	00 764 1055	Metal cylinder	1.4435
9	00 776 1014	Teflon saddle	PTFE
10	52 401 554	Gauge 0-6 bar	
11	20 102 1000	Gauge gasket	Copper
12	20 102 1001	Valve	
13	00 764 1061	Valve nut	Nickel-plated brass
14	20 102 2000	Pressure connector	Nickel-plated brass
15	00 764 1062	Valve body 764	Nickel-plated brass
16	20 300 1002	O-Ring 6.40x1.90	Nitrile
17	52 120 416	Option 437	
18	20 302 1145	O-Ring 17.86x2.62	Viton
19a	20 302 1145	O-Ring 17.86x2.62	Viton
19b	20 304 1017	O-Ring 18.72x2.62	Kalrez
20a	20 302 1146	O-Ring 20.24x2.62	Viton
20b	20 304 1016	O-Ring 20.30x2.62	Kalrez
21	00 777 1053	Scraper ring	Teflon
22a	20 302 1147	O-Ring 18.77x1.78	Viton
22b	20 304 1018	O-Ring 18.77x1.78	Kalrez
23a	20 302 1000	O-Ring 10.77x2.62	Viton
23b	20 304 1000	O-Ring 10.78x2.62	Kalrez

InClean777

1a	00 764 1236	Cable grommet d=5 mm	Neoprene
1b	00 764 1237	Cable grommet d=7 mm	Neoprene
2	00 764 1283	Protective sleeve	Polypropylene
3	52 120 416	Option 437	
4	20 302 1145	O-Ring 17.86x2.62	Viton
5a	20 302 1145	O-Ring 17.86x2.62	Viton
5b	20 304 1017	O-Ring 18.72x2.62	Kalrez
6a	20 302 1146	O-Ring 20.24x2.62	Viton
6b	20 304 1016	O-Ring 20.30x2.62	Kalrez
7	00 777 1053	Scraper ring	Teflon
8a	20 302 1147	O-Ring 18.77x1.78	Viton
8b	20 304 1018	O-Ring 18.77x1.78	Kalrez
9a	20 302 1000	O-Ring 10.77x2.62	Viton
9b	20 304 1000	O-Ring 10.78x2.62	Kalrez

Mettler-Toledo GmbH, Process Analytics

Industrie Nord

CH-8902 Urdorf

Subject to technical changes. Mettler-Toledo GmbH

52900026 A/27 B

Order-No	Designation	No.
Accessories		
52 400 092	Seal set (Viton)	4,5a,6a,7,8a,9a
52 400 093	Seal set (Kalrez)	4,5b,6b,7,8b,9b
90 770 1790	Assembly tool	
00 764 1014	Weld-in socket, Dn 25, L=40, 15°	
52 120 386	Control cable 7 wires ZU 0236 5 m	
52 120 387	Control cable 7 wires ZU 0236 10 m	
52 120 388	Control cable 7 wires ZU 0236 20 m	
52 120 554	Pump with storage tank ZU 0235	
Spare parts		
52 120 390	Position indication switch set ZU0239	
52 120 391	Connection box complete ZU0240	
52 120 392	Water valve ZU0241	
52 120 393	Pneumatic valve ZU0242	
Sensor		
pH-Sensors (a=425 mm):		
InPro4200, InPro3200		
Redox-Sensor:		
PI4805DXK-SB/425		
PI4805-DPA-SC-SB/425		

Mettler-Toledo GmbH, Process Analytics

Industrie Nord
 CH-8902 Urdorf
 Subject to technical changes. Mettler-Toledo GmbH

52900026 A/27 B